

Lithofin KF Silicone Remover

Dissolves silicone residues quickly and easily and makes them easy to remove. Suitable for all solvent- and acid-resistant ceramic tile coverings, sanitary porcelain, glass, acrylic and much more.

Description

Lithofin KF Silicone Remover is a special product based on acids and organic solvents. It dissolves almost all types of silicone, so that they can be pushed off the surface.

Features

Makes silicone residues easy to remove. The thick consistency also allows longer exposure times.

Technical data:

Density: approx. 0.9 g/cm³

pH value: approx. 4

Appearance: light yellow

Odour: non-specific

Solubility in water: partial

Area of application

Lithofin KF Silicone Remover is suitable for cleaning support for silicone stains and for removing old silicone joints.

Substrates

All acid- and solvent-resistant ceramic tiles, sanitary porcelain and glass. Not suitable for natural and artificial stone, various plastics, paints and varnishes, coloured cement joints, wood, aluminium and the like. Alternative waterproofing in the bathroom area protects.

Processing

Cut out old joints, scrape off remnants and layers as much as possible. Shake the bottle well before use. Apply with a brush directly to the dry residues or stains and smooth or distribute.

Layer thickness: approx. 2 mm. Depending on the material, approx. 1 hour, for stubborn residues up to approx. leave on for 8 hours. Then push off the soft silicone with a spatula and wipe the surface clean with a cloth or sponge and remove it completely with a little alcohol. For particularly stubborn soiling, repeat the process with a longer exposure time.

Please note: If in doubt, test in an inconspicuous area.

Surface temperature: 10 to 25°C.

Before inserting a new joint, degrease surfaces well with alcohol.

Storage

Cool and closed. Can be stored for approx. 2 years.

Environmental protection

WGK 1 according to AwSV of 01.08.2017.

Disposal: Container is made of PVC. Rinsed containers can be disposed of via the recyclable material collection system (see note on label).

For information on labelling, transport and disposal, please refer to the safety data sheet.

Packaging units (PU)

a) 500 ml bottle with child-resistant cap
(10 pcs. in a box)

Please note that the environmental and safety information applies to the (concentrated) product in delivery form. If dilution is appropriate for the application, the classification may change. This information can and should only provide non-binding advice. The use of the products must be adapted to the local conditions and the conditions to be treated, surfaces. If there is no experience and in all cases of doubt, the product should be tried out in an inconspicuous place beforehand. (AUS-NZ2.26/9.25)